#### Denton Digital Building Intelligence PoE Lighting Install Kit

DENT-LK-C2-B (2x 4" GIMBAL LIGHTS)

PACKING LIST			
QTY	SKU OR ID	DETAILS	
1	DENT-LINC-CC	LED CONTROL DRIVER	
1	GPOE-1AB-56V60W	PoE 60 WATT INJECTOR WITH Y CABLE	
1	DENT-WS-S4	4 BUTTON CONTROL SWITCH	
2	DWN-4-RDG-WH	4" GIMBAL DOWNLIGHT	









## Denton Contracto Ighting Kit

DATE: March 18, 2022

DENT-LK-C2-B
Bill of Materials

**DRAWING NUMBER:** 

00





#### **General Layout**

#### **INSTRUCTIONS:**

OR

CAT 6

Optional Data Signal

- Locate where the Power Sourcing Equipment (PSE) will be located within 330 ft (100m) of the lighting controller location

Cable

**Power Sourcing Equipment:** The DENT-LK-C2-B is provided with a 60 watt PoE injector. You may also connect to any IEEE 802.3bt Type 3 or Type 4 PoE

switch. Please contact PoE Texas for recommended compatible devices.

GPOE-1AB-56v60w Injector: Must be mounted within 330 ft (100m) of DENT-LINC

**DENT-WS-S4:**Must be mounted within 100 ft (30m) of DENT-LINC

- Locate and install the DENT-LINC within 100 ft of the final location of the lights and controller. You can install it in the ceiling or in a centralize control room
- Run wiring and install light fixtures and controller



**INSTALLATION:** You call find all of the cables, connectors, wall boxes, and tools to install the DENT-LK-C2-B in the DENT-LK-Install-Kit



## Denton Contrac Lighting Kit

DATE: March 18, 2022

TITLE:

DENT-LK-C2-B Layout

**DRAWING NUMBER:** 

01

#### **DENT-LK-C2-B**



# Denton Contractor Lighting Kit

DATE:


March 18, 2022

TITLE:
DENT-LK-C2-B

Wiring

**DRAWING NUMBER:** 

02



C -> Blue -> V-

### DENT-LK-C2-B Wiring CCT Fixtures

3000K					
CCT Fixture Wires	18-2 Wires	LINC Output Harness			
Warm + [Brown]	red	Output 3 [Red]	Output 4 [Red]		
Warm - [Blue]	black	Output 3 [Black]	Output 4 [Black]		
Cool + [Red]	Not connected				
Cool - [Black]	Not connected				
4000K					
CCT Fixture Wires	18-2 Wires	LINC Output Harness			
Warm + [Brown]	red	Output 3 [Red]	Output 4 [Red]		
Warm - [Blue]	black	Output 3 [Black]	Output 4 [Black]		
Cool + [Red]	red	Output 3 [Red]	Output 4 [Red]		
Cool - [Black]	black	Output 3 [Black]	Output 4 [Black]		
4000K					
CCT Fixture Wires	18-2 Wires	LINC Output Harness			
Warm + [Brown]	Not connected				
Warm - [Blue]	Not connected				
Cool + [Red]	red	Output 3 [Red]	Output 4 [Red]		
Cool - [Black]	black	Output 3 [Black]	Output 4 [Black]		



## Denton Contracto Lighting Kit

DATE: March 18, 2022

DENT-LK-C2-B
Wiring CCT

**DRAWING NUMBER:** 

03