

Installation Instructions




- This product is designed to be wall mounted or DIN rail mounted
- Use CAT 5e or CAT 6 or better cables
- The device needs sufficient cooling to operate at maximum power output. Refer to the online manual for specification
- Allow for sufficient airflow around the device

For installation, wiring, and configuration information, please refer to the on-line technical manual for this device by scanning this QR code or visiting:

https://www.poetexas.com/gbts-10-8-m_rev2/




Installation Options



DIN Mounted with x2 PS-48v480w

Installation Notes:

- Properly tighten set screws to hold cables in switch and power supply



Wall Mounted with Remote Power

SWITCH SIDE	WIRE COLOR	POWER SUPPLY SIDE
V1 P+	RED	V+
V1 P-	BLACK	V-
V2 P+	RED	V+
V2 P-	BLACK	V-

AC POWER	WIRE COLOR	POWER SUPPLY SIDE
120 VAC 50/60Hz Minimum 1 amps	WHITE	N
	BLACK	L
	GREEN	GROUND

GBTS-10-8-M
Installation Drawings

3616 Far West Blvd
Suite 117-294
Austin TX 78731

DATE: 11-20-2025

TITLE: **PRODUCT DRAWINGS**

DRAWING NUMBER:

A